



## 液晶フード LCD Hood Pare-soleil LCD 液晶屏罩

取扱説明書 / Operating Instructions/  
Mode d'emploi/Bedienungsanleitung/  
Manual de instrucciones/Gebruiksaanwijzing/  
Bruksanvisning/Manual de instruções/  
Istruzioni per l'uso/Инструкция по эксплуатации/  
使用説明書 / 使用说明书 / 사용설명서 /  
توضیحات الشامل







### SH-L1AM

© 2009 Sony Corporation Printed in Japan

<http://www.sony.net/>

この説明書は、古紙70%以上の再生紙と、  
VOC(揮発性有機化合物)ゼロ植物油型  
インキを使用しています。

Printed on 70% or more recycled paper  
using VOC (Volatile Organic  
Compound)-free vegetable oil based ink.



### 日本語

お買い上げいただきありがとうございます。

ご使用の前にこの取扱説明書をお読みください。お読みになったあとは、いつでも見られるところに必ず保管してください。

この液晶フード(以下本機とする)はソニーαカメラ  
DSLR-A380/A330/A230(以下、カメラとする)専用です。

#### △注意 安全のために

ソニー製品は、安全に充分考慮されています。しかし、間違った使い方をすると、人身事故が起る恐れがありますので、事故を防ぐために次のことを必ず守りください。

- 安全のための注意事項を守る。
- 故障したら使い方に相談する。

#### 警告表示の意味

この取扱説明書や製品では、次のような表示をしています。

#### △注意


この表示の注意事項を守らないと、事故によりけりを起こすことがあります。



禁止

#### △注意 下記の注意事項を守らないと けがをすることがあります。

カメラに装着した状態で本機だけを持たない  
本機がはずれてカメラが壊れたり、思わずけがをする  
ことがあります。



禁止

フードを開いたままマニュアルアーマーを調かない  
フードが顔に当たりけがをすることがあります。



禁止

#### 主な特長

- 液晶画面への不要な光の映り込みを防ぎ、屋外での撮影などで液晶画面の視認性を高めます。
- フード内部に反射防止処理がされているためフード部が映り込みにくく、液晶画面の視認性を高めます。
- フードははずすと、液晶保護カバーとして使うことができます。
- 撮影状況に応じて、逆さに取付けて使うこともできます。(イラストA)

#### 使用上のご注意

三脚使用など液晶画面の可動範囲が狭くなる場合があります。

#### 各部の名前 B

- 1 液晶保護カバー 2 アタッチメント 3 正面フード  
4 側面フード

#### 液晶フードを使う

#### 取り付ける C

本機下部のツメをカメラの凹部に合わせて、本機上部を力  
で突っ込むまで押して取り付ける。

#### フードを開閉する D

正面フードをゆっくりと持ち上げて、フードを開きます。  
閉じるときは、側面フードを閉じた後、正面フードを閉じます。

#### When the panels come away from the attaching frame

本機下部の両端を押し上げながら本機上部の両端を持ち上  
げる。  
本機を持ち上げるとカメラが落しないように、しっかりと  
と支えてください。

#### フードがはずれてしまったときは

過剰な力を加えると、破損を防ぐためフードがはずれるこ  
とがあります。その場合は、液晶保護カバーからアタッチメ  
ントを取りはずし、以下の手順で付け直してください。

#### Notes

本機下部の両端を押し上げながら本機上部の両端を持ち上  
げる。

本機を持ち上げるとカメラが落しないように、しっかりと  
と支えてください。

#### Using as an LCD protective cover

With the LCD hood attached to the camera, detach the  
attaching frame by sliding it in the direction of the arrow.  
(Illustration G)

To reattach the LCD hood, slide the attaching frame in the  
reverse direction until it clicks into place.

#### How to clean the LCD protective cover

Brush off any dust from the surface of the LCD protective  
cover with a blower brush or soft brush. Wipe off fingerprints  
or other smears with a soft cloth.

#### お手入れのしかた

液晶保護カバー表面についてほこりは、プロワーブラシを柔  
らかい刷毛で取ってください。指紋その他の汚れは、柔らか  
い布で拭き取ってください。

#### ご注意

・液面上部アタッチメント中央の溝に押し込みながら、  
アタッチメント上下の溝に側面フードの突きをはめこみます。

・バネの先端が溝に入っていないと側面フードは開きません。  
開かない場合は、バネの先端が溝に入るよう付直してください。

#### Specifications

Dimension 71 × 54 × 8.5 mm (w/h/d)  
(Approx.) (2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Mass (Approx.) 20g (0.7oz)

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

Included items LCD hood (1), LCD protective cover (1), Set  
of printed documentation

Design and specifications are subject to change without notice.

Dimensions (Aprox.) 71 × 54 × 8.5 mm (w/h/d)  
(2 7/8 × 2 1/4 × 11/32 inches)  
(when the hood is closed)  
(excluding the projecting parts)

Weight (Aprox.) 20g

